

56



Insulated busbar 2P 63A fork 10mm² 57M

Technical properties

Number of modules

Electric current	
Rated current	63 A
Architecture	
Number of poles	2
Dimensions	
Length	1,000 mm
Voltage	
Rated impulse withstand voltage Uimp	4,500 V
Connection	
Cross-section rigid conductor	10 mm²
Connector/plug type	Phase busbar with fork
Capacity	

KDN263B