



KDN263B

Insulated busbar 2P 63A fork 10mm² 57M

Technical properties

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	2
-----------------	---

Dimensions

Length	1,000 mm
--------	----------

Voltage

Rated impulse withstand voltage Uimp	4,500 V
--------------------------------------	---------

Connection

Cross-section rigid conductor	10 mm²
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	56
-------------------	----