



KDN280B

Insulated busbar 2P 80A fork 16mm² 57M

Technical properties

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	2
-----------------	---

Dimensions

Length	1,000 mm
--------	----------

Voltage

Rated impulse withstand voltage Uimp	4,500 V
--------------------------------------	---------

Connection

Cross-section rigid conductor	16 mm²
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	57
-------------------	----