

57



Insulated busbar 3P 63A fork 10mm<sup>2</sup> 57M

**Technical properties** 

**Electric current** 

Rated current 63 A

**Architecture** 

Number of poles 3

**Dimensions** 

Length 1,000 mm

Voltage

Rated impulse withstand voltage Uimp 4,500 V

Connection

Cross-section rigid conductor 10 mm<sup>2</sup>

Connector/plug type Phase busbar with fork

Capacity

Number of modules

KDN363B