



KDN380B

**Insulated busbar 3P 80A fork 16mm<sup>2</sup> 57M**

**Technical properties**

**Electric current**

Rated current	80 A
---------------	------

**Architecture**

Number of poles	3
-----------------	---

**Dimensions**

Length	1,000 mm
--------	----------

**Voltage**

Rated impulse withstand voltage Uimp	4,500 V
--------------------------------------	---------

**Connection**

Cross-section rigid conductor	16 mm <sup>2</sup>
Connector/plug type	Phase busbar with fork

**Capacity**

Number of modules	57
-------------------	----