



KDN451E

Insulated busbar 3x(P+N) 80A fork 16mm² 54M

Technical properties

Electric current

Rated current 80 A

Architecture

Number of poles 4

Dimensions

Length 1,000 mm

Voltage

Rated impulse withstand voltage Uimp 4,500 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 54