



KJ01C

Brass busbar terminal 125A, 4pole, 2x 10-35mm² / 10 x 2,5-16² per pole

Technical properties

Electric current

Rated current	125 A
---------------	-------

Architecture

Number of poles	4
-----------------	---

Dimensions

Height	86 mm
Width	129 mm
Depth	44 mm

Capacity

Number of modules	7.50
-------------------	------

Internal use only

Number of half modules of 17,5 mm	15
-----------------------------------	----

Installation, mounting

Nominal tightening torque	1.50 - 1.50 Nm
---------------------------	----------------