

-40 - 80 °C



MZ201



## Auxiliary contact 1C+10 6A 240V AC

## **Technical properties**

FI	ectric	current	

Rated current	6 A
---------------	-----

### Connectivity

Type of connection	Screw terminal
Mounting type	Click mounting

### Capacity

Number of modules	0.50
Number of modules	0.50

### Connection

Type of contacts	1NC+1NO
Cross-section flexible conductor	6 mm²
Cross-section rigid conductor	10 mm²

### Voltage

Rated insulation voltage Ui	4,000 V
Type voltage supply	AC

## **Endurance**

Number of mechanical operations	12,000
Electric endurance in number of cycles	6,000

## Electric endurance in number of cycles

Storage/transport temperature

Use conditions	
Operating temperature	-25 - 60 °C

# Power

Total nower loss under IN	0.10 W

#### **Dimensions**

Height	80 mm
Width	9.50 mm
Depth	40 mm

## **Equipment**

Number of INV contacts	0

Number of NC contacts