





Alarm contact 1C+10 6A 240V AC

Technical properties

Rated current		6 A
Rateu Current		O F

Connectivity

Type of connection	Screw terminal
Mounting type	Click mounting

Capacity

Connection

Type of contacts	1NC+1NO
Cross-section flexible conductor	6 mm²
Cross-section rigid conductor	10 mm²

Voltage

Rated insulation voltage Ui	4,000 V
Type voltage supply	AC

Endurance

Use conditions

Number of mechanical operations	12,000
Electric endurance in number of cycles	6,000

Operating temperature	-25 - 60 °C
Storage/transport temperature	-40 - 80 °C

Power

Total power loss under IN	0.20 W
---------------------------	--------

Dimensions

Width	9 mm
Depth	68 mm

Equipment

Number of INV contacts	0
Number of NC contacts	1

Number of NC contacts