




SK602



## Voltmeter switch 3"o

### Technical properties

#### Electric current

Rated current	20 A
---------------	------

#### Capacity

Number of modules	3
-------------------	---

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Connection

Cross-section flexible conductor	1.5 - 10 mm <sup>2</sup>
Cross-section rigid conductor	1 - 6 mm <sup>2</sup>

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Dimensions

Height	85 mm
Width	70 mm
Depth	64 mm

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Installation, mounting

Mounting on	DIN rail
-------------	----------

#### Voltage

Rated insulation voltage Ui	690 V
-----------------------------	-------