



SPN715D

SPD 2P auto-protected pluggable 15kA class 2 with end of life indicator

Technical properties

Capacity

Number of modules	2
-------------------	---

Voltage

Rated operational voltage Ue	230 - 230 V
------------------------------	-------------

Continuous operating voltage Uc according to IEC 61643-1	275 V
--	-------

Voltage protection level Up according to IEC 61643-1	1.50 kV
--	---------

Electric current

Nominal discharge current In 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	5 kA, 20 kA
---	-------------

Max. discharge (Imax) L-N(PEN)/ N-PE	15 kA
--------------------------------------	-------

Dimensions

Height	82 mm
--------	-------

Width	44 mm
-------	-------

Depth	103 mm
-------	--------

Use conditions

Operating temperature	-40 - 55 °C
-----------------------	-------------

Network configuration

Network type	TN, TT
--------------	--------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------