



SRC04005

Bar/Cable-through Current Transformer BG 113 400/5A 5VA Class 1

Technical properties

Specific identification attributes for Protection

Filter Type product Plug-in current transformer

Functions

Accuracy class 1

Power

Power 5 VA

Total power loss under IN 3.60 W

Dimensions

Height 70 mm

Width 50 mm

Depth 30 mm

Height of opening 20 mm

Width of opening 29.50 mm

Connectivity

Type of connection Screw terminal

Frequency

Frequency 50 - 60 Hz

Voltage

Rated insulation voltage U_i 3,000 V

Use conditions

Operating temperature -40 - 40 °C

Storage/transport temperature -40 - 40 °C

Connection

Cross-section flexible conductor 1.5 - 6 mm²

Cross-section rigid conductor 1.5 - 6 mm²

Safety

Ingress Protection (IP) class IP10

Electric current

Max. intensity of primary 400 A

Max. intensity of secondary 5 A

Installation, mounting

