







## Safety transformer 25VA 230V/12-24V

## **Technical properties**

V	lta	a	۵

Output voltage	12 - 24 V
Rated operational voltage Ue	230 - 230 V
Rated insulation voltage Ui	4,000 V
Power	
Power consumption VA	25 VA
Connection	
Cross-section flexible conductor	4 mm²
Cross-section rigid conductor	6 mm²
Frequency	
Frequency	50 - 50 Hz
Installation, mounting	
Mounting on	DIN rail
Use conditions	
Operating temperature	-20 - 35 °C
Capacity	
Number of modules	4
Dimensions	
Height	85 mm
Width	70 mm
Depth	58 mm
Safety	
Ingress Protection (IP) class	IP20
Temperature protection	Yes
Equipment	
Is short-circuit protected	Yes
On/off switch	No