



ST312



## Safety transformer 25VA 230V/12-24V

### Technical properties

#### Voltage

Output voltage	12 - 24 V
Rated operational voltage U <sub>e</sub>	230 - 230 V
Rated insulation voltage U <sub>i</sub>	4,000 V

#### Power

Power consumption VA	25 VA
----------------------	-------

#### Connection

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Installation, mounting

Mounting on	DIN rail
-------------	----------

#### Use conditions

Operating temperature	-20 - 35 °C
-----------------------	-------------

#### Capacity

Number of modules	4
-------------------	---

#### Dimensions

Height	85 mm
Width	70 mm
Depth	58 mm

#### Safety

Ingress Protection (IP) class	IP20
Temperature protection	Yes

#### Equipment

Is short-circuit protected	Yes
On/off switch	No