




ST314



Safety transformer 40VA 230V12-24V

Technical properties

Voltage

Output voltage	12 - 24 V
Rated operational voltage U_e	230 - 230 V
Rated insulation voltage U_i	4,000 V

Power

Power consumption VA	40 VA
----------------------	-------

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Frequency

Frequency	50 - 50 Hz
-----------	------------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Use conditions

Operating temperature	-20 - 35 °C
-----------------------	-------------

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	85 mm
Width	70 mm
Depth	58 mm

Safety

Ingress Protection (IP) class	IP20
Temperature protection	Yes

Equipment

Is short-circuit protected	Yes
On/off switch	No