



TJA470

Domovea expert

Technical properties

Equipment

| | |
|--------------------|-----|
| Web server | Yes |
| Number of channels | 1 |

Voltage

| | |
|----------------------------|-----------|
| Operating voltage | 24 - 24 V |
| Operating voltage over bus | 21 - 32 V |
| Type voltage supply | DC |

Connectivity

| | |
|--|--------------------|
| Type of interface bus system/media gateway | Multiple interface |
|--|--------------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

Dimensions

| | |
|-----------------------|---|
| Number of width units | 6 |
|-----------------------|---|

Texts

| | |
|--------------------|--|
| Encoding | Management of 4 configurable user profiles |
| Function | Local and remote connection of the door station with IP end devices, such as smartphones, tablet computers and PCs |
| Labelling | Large labelling field |
| Type of connection | With quickconnect plug-in terminals |