



TJA670



Domovea basic

Technical properties

Equipment

Web server	Yes
Number of channels	1

Voltage

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC

Connectivity

Type of interface bus system/media gateway	Multiple interface
--	--------------------

Settings

Supported configuration mode	ETS, easy
------------------------------	-----------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Width	105 mm
Depth	65 mm
Number of width units	6

Texts

Encoding	Management of 4 configurable user profiles
Installation mode	For installation in distribution box
Labelling	With labelling field
Type of connection	With quickconnect plug-in terminals
Voltage	Power supply via PoE or 24 V DC