



TJA670





Domovea basic

Technical properties

	-		:	-	-	-	-	a
_	u	u		IJ	ш	ıe	п	ı

Web server	Yes
Number of channels	1

Voltage

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC

Connectivity

Type of interface bus system/med	ia
gateway	Multiple interface

Settings

Supported configuration mode	ETS, easy

Safety

Ingress Protection (IP) class	IP20

Use conditions

-5	- 45	00
	-5	-5 - 45

Controls and indicators

With LED indication	Yes

Dimensions

Width	105 mm
Depth	65 mm
Number of width units	6

Texts

Encoding	Management of 4 configurable user profiles
Installation mode	For installation in distribution box
Labelling	With labelling field
Type of connection	With quickconnect plug-in terminals
Voltage	Power supply via PoE or 24 V DC