



TRE302



RF external double push button wall mounted

Technical properties

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Frequency

Radio transmission frequency	868.30 MHz
------------------------------	------------

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Connectivity

Receiver category	2
Radio protocol	KNX Radio

Functions

With room temperature controller	No
----------------------------------	----

Voltage

Operating voltage	3 - 3 V
-------------------	---------

Dimensions

Built-in depth flush-mounted boxes	25 mm
Height	76 mm
Width	49 mm

Materials

Colour	White
RAL code	9010
Material	Plastic
Surface finish	Glossy, Mat

Accessories

Has labelling field	No
---------------------	----

Texts

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control, Configuration can simply be transferred from a master device, Reset function (to factory setting)
Installation mode	For screw fastening or For mounting with adhesive mounting, For vertical and horizontal mounting