



TRM693G



Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio

Technical properties

Connectivity

Radio protocol	KNX Radio
Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

Settings

Supported configuration mode	ETS, easy, quicklink
------------------------------	----------------------

Dimensions

Depth	22 mm
Built-in depth	40 mm

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

Electric current

Rated current	3 A
---------------	-----

Frequency

Frequency	50 - 50 Hz
Radio reception frequency	868.30 - 868.30 MHz

Power

Output power	690 W
--------------	-------

Voltage

Operating voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V
System supply voltage	230 V AC

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Texts

Function	Easy additional functions: +6 scenes, Repeat function can be activated to increase the radio range, Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals