



TX211A



Dimmer 3 outputs KNX, 1/10V

Technical properties

Voltage

Operating voltage over bus	21 - 32 V
System supply voltage	30 V DC Via bus

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Equipment

Number of outputs	3
Type of dimmer	1 - 10 V

Capacity

Number of modules	4
-------------------	---

Power

230 V incandescent and halogen lamp	2,300 W
Power of variator	0 - 2,300 W

Connectivity

With bus system KNX radio	No
Type of connection	Screw terminal

Settings

Supported configuration mode	ETS
------------------------------	-----

Texts

Type of connection	With screw terminals
--------------------	----------------------