



VB8101PSPD

Vega 2Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

Technical properties

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Functions

Has protection main switch	No
Overvoltage protection	Yes

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	36
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth	145 mm
Height	450 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm

Cover, door

Interlockable	Yes
Door/cover is transparent	Yes

Materials

RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	3
Number of RCCB in enclosure	1

Equipment

Number of light groups	2
Number of rows	2
With energy meter	No
Number of rails	2
With bell transformer	No
Safety	
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40