



VB8101TSPD

**Vega 2Row 7W 1RCD - 2x6A Ltg. RCBOs SPD**

**Technical properties**

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No

**Functions**

Has protection main switch	No
Overvoltage protection	Yes

**Configuration**

Number of arc fault detection devices AFDD	0
--	---

**Capacity**

Number of modules	36
-------------------	----

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth	145 mm
Height	450 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm

**Cover, door**

Interlockable	Yes
Door/cover is transparent	Yes

**Materials**

RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	3
Number of RCCB in enclosure	1

**Equipment**

Number of light groups	2
Number of rows	2
With energy meter	No
Number of rails	2
With bell transformer	No
<b>Safety</b>	
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40