



VBE108101TSPD

**Vega,4Row,5/8 WAY SPLIT LOAD CU,T/DOOR,2P ISOLATOR,SPD,1xRCD,2x6A LIGHTING
RCBOs**

Technical properties

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Functions

Has protection main switch	No
Overvoltage protection	Yes

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	72
-------------------	----

Electric current

Rated current	80 A
---------------	------

Dimensions

Depth	145 mm
Height	750 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm

Cover, door

Interlockable	Yes
Door/cover is transparent	Yes

Materials

RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	3
Number of RCCB in enclosure	1

Equipment	
Number of light groups	2
Number of rows	4
With energy meter	No
Number of rails	4
Extension possible	Yes
With bell transformer	No
Safety	
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Protection class	Isolation class II