



VC02SW

Enclosed Switch Disconnect

Technical properties

Architecture

Number of poles 2

Voltage

Type voltage supply AC

Rated insulation voltage U_i 240 V

Electric current

Rated current 100 A

Use conditions

Degree of pollution according to IEC 60664 /
IEC 60947-2 2

Capacity

Number of modules 2