



VF8101SPD

Volta 2Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

Technical properties

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	2
Number of rows	2
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	24
-------------------	----

Dimensions

Height	505.50 mm
Width	348 mm
Depth	94.50 mm
Built-in width	314 mm
Built-in depth	89 mm
Number of width units	12

Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	No

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Safety

Protection class	Isolation class II
------------------	--------------------

Subject to technical modifications

Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Snap on lock
Glow wire test	650 °C