



WFDP50VNBSB



50A Double Pole Switch 2 Gang with LED Indicator Brushed Steel Black Insert

Technical properties

Electric current

Rated current 50 A

Installation, mounting

Mounting on Flush mounting

Materials

Colour Stainless steel

Surface finish Mat

Material Stainless steel

Treatment Brushed

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Built-in depth 29.10 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Texts

Lighting With control LED for ON

Switch mode 2-pole