



WFS51BSB



**5A 1 Gang Unswitched Socket Brushed Steel Black Insert**

**Technical properties**

**Electric current**

Rated current	5 A
---------------	-----

**Voltage**

Rated voltage	250 V
---------------	-------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Dimensions**

Height	86 mm
Width	86 mm
Depth	25 mm

**Materials**

Colour	Stainless steel
Surface finish	Mat
Material	Stainless steel

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Equipment**

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	0
-------------------	---

**Texts**

Imprint	Without imprint
---------	-----------------

---

Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

---