



WFSS82BSB



### 13A 2 Gang Double Pole Switched Socket Brushed Steel Black Insert

#### Technical properties

##### Electric current

Rated current	13 A
---------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Dimensions

Height	86 mm
Width	146 mm
Depth	29 mm

##### Materials

Colour	Stainless steel
Surface finish	Mat
Material	Stainless steel

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	0
-------------------	---

##### Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection