



WMCS11



## 6A Ceiling Switch 1 Way

### Technical properties

#### Electric current

Rated current	6 A
---------------	-----

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	0
-------------------	---

#### Dimensions

Built-in depth	0
----------------	---

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Pull cord
---------------------------	-----------

#### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	1-way