



WMCS3PIF



10A 3P Ceiling Switch Marked FAN & ISOLATOR

Technical properties

Electric current

Rated current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 0

Dimensions

Built-in depth 23 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Pull cord

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 3-pole