



WMGKS/EL



## 20A Double Pole Key Switch Marked 'EM LTG TEST'

### Technical properties

#### Voltage

Rated voltage	250 V
---------------	-------

#### Architecture

Number of poles	2
-----------------	---

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Controls and indicators

Number of buttons	0
-------------------	---

With feedback signal contact	No
------------------------------	----

#### Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

Transparent	No
-------------	----

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Dimensions

Depth	24 mm
-------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Texts

Imprint	With imprint
---------	--------------

Lighting	Without neon lamp
----------	-------------------

Related Systems	Hager sollysta
-----------------	----------------