



WMGS12PSB



## 20A 2 Way Single Pole Switch Polished Steel Black Insert

### Technical properties

#### Electric current

|                   |      |
|-------------------|------|
| Switching current | 20 A |
| Rated current     | 20 A |

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Materials

|                |                 |
|----------------|-----------------|
| Colour         | Silver          |
| Surface finish | Glossy          |
| Material       | Stainless steel |

#### Identification

|                      |  |
|----------------------|--|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|--|

#### Connectivity

|               |                   |
|---------------|-------------------|
| Mounting type | Snapp-on mounting |
|---------------|-------------------|

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

#### Dimensions

|                |          |
|----------------|----------|
| Built-in depth | 13.10 mm |
|----------------|----------|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

#### Texts

|             |  |
|-------------|--|
| Lighting    | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole                                   |