



WMMTVF

### Single IEC Female Euromodule White

#### Technical properties

##### Connectivity

Mounting type	Snapp-on mounting
---------------	-------------------

##### Attenuation

Tap loss at 860 MHz	0.30 dB
---------------------	---------

##### Connection

Connector/plug type	Direct socket
---------------------	---------------

##### Frequency

Frequency bandwidth	5 - 860 MHz
---------------------	-------------

##### Equipment

Number of outputs	1
-------------------	---

##### Materials

Material	Urea formaldehyde
Colour	White

##### Dimensions

Depth	24 mm
-------	-------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------