




WMMTVMB



Single IEC Male Euromodule Black

Technical properties

Connectivity

Mounting type Snapp-on mounting

Attenuation

Tap loss at 860 MHz 0.30 dB

Connection

Connector/plug type Direct socket

Frequency

Frequency bandwidth 5 - 860 MHz

Equipment

Number of outputs 1

Materials

Material Urea formaldehyde

Colour White

Dimensions

Depth 24 mm

Installation, mounting

Mounting on Flush mounting

Identification

Assembly arrangement Basic element with full cover plate