



WMPS12RW



## Push Switch Wide Rocker Grey

### Technical properties

#### Electric current

|                           |      |
|---------------------------|------|
| Switching current         | 10 A |
| Momentary contact current | 10 A |

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Architecture

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Controls and indicators

|                              |                    |
|------------------------------|--------------------|
| Number of buttons            | 1                  |
| Type of push button          | Single push button |
| With feedback signal contact | No                 |

#### Materials

|                |                   |
|----------------|-------------------|
| Colour         | White             |
| Surface finish | Glossy            |
| Material       | Urea formaldehyde |
| Treatment      | Coated            |
| Transparent    | No                |

#### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

#### Dimensions

|       |       |
|-------|-------|
| Depth | 24 mm |
|-------|-------|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Texts

|                   |  |
|-------------------|--|
| Imprint           | Without imprint                            |
| Installation mode | For flush-mounted and hollow wall mounting |
| Switch mode       | NO contact                                 |