



WPSSU83FO



13A FCU Switched with Flex Outlet

Technical properties

Electric current

Rated current	13 A
---------------	------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Grey
Surface finish	Glossy
Material	Steel
Treatment	Epoxy

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole