



WXPPS22



IP66 10AX 2 Gang 2 Way Switch

Technical properties

Electric current

Switching current	10 A
Rated current	10 A

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Light grey
Surface finish	Mat
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	2
-------------------	---

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way