



WXPS81



IP66 Single 13A Un-switched Socket

Technical properties

Electric current

Rated current	13 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Dimensions

Height	116.50 mm
--------	-----------

Width	103 mm
-------	--------

Depth	88.25 mm
-------	----------

Materials

Colour	Light grey
--------	------------

Surface finish	Glossy
----------------	--------

Material	Polycarbonate (PC)
----------	--------------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	Yes
-----------------	-----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection
Cover, door	
Type of lid	Hinged cover falls back, manual clip-in