



10112189

## Frame 1gang, R.1, p. white glossy

### Technical properties

#### Dimensions

Depth	9.9 mm
Height	80.7 mm
Width	80.7 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Colour of labelling	105,105,105
Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Material for printing	ASA polar white
Surface appearance	glossy
Type of surface treatment	untreated

#### Installation, mounting

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

#### Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Identification

Main design line	Berker R.1
------------------	------------

#### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---