



10112214

**Frame 1gang, R.3, stainless steel/p. white**

**Technical properties**

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 9.9 mm  |
| Height | 81.2 mm |
| Width  | 81.2 mm |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

**Materials**

|                           |                             |
|---------------------------|-----------------------------|
| Colour of design line     | stainless steel/polar white |
| Colour                    | stainless steel             |
| Colour                    | stainless steel optics      |
| RAL colour                | RAL 9022 - Pearl light grey |
| Material                  | stainless steel             |
| Surface appearance        | matt                        |
| Type of surface treatment | untreated                   |

**Installation, mounting**

|                   |  |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|