



10112339

**Frame 1gang, R.1, orange trans./p. white glossy, acrylic**

**Technical properties**

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 9.9 mm  |
| Height | 81.2 mm |
| Width  | 81.2 mm |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

**Materials**

|                              |                                |
|------------------------------|--------------------------------|
| Design lines special colours | orange transparent/polar white |
| Material / workmanship       | acrylic                        |
| Surface appearance           | glossy                         |
| Type of surface treatment    | untreated                      |

**Installation, mounting**

|                   |  |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
| Information text  | Not suitable for water-protected, flush-mounted installation IP44.  |