



10116062

Frame 1gang, Q.1, red velvety

Technical properties

Dimensions

| | |
|--------|---------|
| Depth | 9.9 mm |
| Height | 80.5 mm |
| Width | 80.5 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|---------------------|
| Design lines special colours | red |
| Colour | red |
| Colour | red |
| RAL colour | RAL 3003 - Ruby red |
| Material | duroplastic |
| Surface appearance | velvety |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker Q.1 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|