



10122116

**Frame 2gang, R.1, glass black**

**Technical properties**

**Dimensions**

|        |          |
|--------|----------|
| Depth  | 9.9 mm   |
| Height | 152.2 mm |
| Width  | 81.2 mm  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

**Materials**

|                           |             |
|---------------------------|-------------|
| Colour of design line     | glass black |
| Surface appearance        | glossy      |
| Type of surface treatment | untreated   |

**Installation, mounting**

|                   |  |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker R.1 |
|------------------|------------|

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|