



10122204

Frame 2gang, R.3, stainless steel/black

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 152.2 mm |
| Width | 81.2 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

Materials

| | |
|---------------------------|-----------------------------|
| Colour of design line | stainless steel/black |
| Colour | stainless steel |
| Colour | stainless steel optics |
| RAL colour | RAL 9022 - Pearl light grey |
| Material | stainless steel |
| Surface appearance | matt |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | for vertical and horizontal mounting, clamp fastening |
|-------------------|---|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Identification

| | |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|