



10122245

**Frame 2gang, R.3, black glossy**

**Technical properties**

**Dimensions**

Depth	9.9 mm
Height	151.75 mm
Width	80.75 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	---

**Settings**

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

**Equipment**

Type of configuration	Laserdruck
-----------------------	------------

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

Main design line	Berker R.3
------------------	------------

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---