



10122269

Frame 2gang vert., lab. field, R.3, p. white glossy

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 151.7 mm |
| Width | 80.7 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

Materials

| | |
|---------------------------|-----------------------|
| Colour of labelling | 105,105,105 |
| Colour of design line | polar white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material for printing | ASA polar white |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|-----------------|
| Installation mode | clamp fastening |
|-------------------|-----------------|

Settings

| | |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter | R1_weiß |

Equipment

| | |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

Use

| | |
|--|----------------------|
| Differentiation characteristic 1 - Sales | with labelling field |
|--|----------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker R.3 |
|------------------|------------|

Instructions

| | |
|------------------|--|
| Information text | Labelling field height arranged for P-touch strips 6 mm. |
|------------------|--|