



10142145

Frame 4gang, R.1, black glossy

Technical properties

Dimensions

Depth	9.9 mm
Height	293.7 mm
Width	80.7 mm

Capacity

Number of sockets	4
-------------------	---

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Type of surface treatment	untreated

Installation, mounting

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	-------------------------------------------------------

Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

Safety

Protection index IP	IP20
---------------------	------

Identification

Main design line	Berker R.1
------------------	------------

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---------------------------------------------------------------------------------------------------------------------------------