



10142189

**Frame 4gang, R.1, p. white glossy**

**Technical properties**

**Dimensions**

Depth	9.9 mm
Height	293.7 mm
Width	80.7 mm

**Capacity**

Number of sockets	4
-------------------	---

**Materials**

Colour of labelling	105,105,105
Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Material for printing	ASA polar white
Surface appearance	glossy
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

**Settings**

Shading parameter	R1_biały
Laser parameter	R1_weiß

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Identification**

Main design line	Berker R.1
------------------	------------

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---