



10142245

### Frame 4gang, R.3, black glossy

#### Technical properties

##### Dimensions

Depth	9.9 mm
Height	293.7 mm
Width	80.7 mm

##### Capacity

Number of sockets	4
-------------------	---

##### Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Type of surface treatment	untreated

##### Installation, mounting

Installation mode	for vertical and horizontal mounting, clamp fastening
-------------------	---

##### Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

##### Equipment

Type of configuration	Laserdruck
-----------------------	------------

##### Safety

Protection index IP	IP20
---------------------	------

##### Identification

Main design line	Berker R.3
------------------	------------

##### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---